


IP Protected Bench Scale KERN FXN · FXN-M



## Bench scale, protected by stainless steel and protection type IP68, verification optional

### Features

- Ideal for the increased hygienic requirements in the food industries
- Your support in a HACCP-compliant quality system
- Ideal for the robust industrial applications
- Thanks to the stainless steel design of the housing and platform with smooth surface, the scale is rust-free and easy to clean
- **1** Dust and splash water protection type IP68. Therefore very robust and durable. Ideal for rough environmental conditions. Even immersion of the scale in water possible
- Very fast display: steady weight values within 2 s
- High mobility: thanks to battery operation, compact, lightweight construction, it is suitable for the use in several locations (kitchens, sales offices, cafeterias, food industry laboratories, etc.)

- **2** Recessed grips on the underside of the scale for easy transportation
- Weighing with tolerance range (checkweighing): a visual and audible signal helps with portioning, dispensing or grading

### Technical data


- Large backlit LCD display, digit height 25 mm
- Dimensions weighing surface, stainless steel, WxD 236x195 mm
- Ready for use: Batteries standard, 4x1.5 V Size D, operating time approx. 500 h, AUTO-OFF function to preserve the battery
- Net weight approx. 3,4 kg
- Permissible ambient temperature -10 °C/40 °C

### Accessories

- **3** Tare pan made from stainless steel, ideal for weighing loose small parts as well as fruits, vegetables, etc., overall dimensions WxDxH 400x300x45 mm, KERN RFS-A02

Note: Official verification is mandatory for commercial trade

#### STANDARD



#### OPTION



#### FACTORY



Model	Weighing capacity [Max]	Readability [d]	Verification value [e]	Minimal load [Min]	Smallest part weight (Normal) g/piece	Options	
						Verification	DAkkS Calibr. Certificate
KERN	kg	g	g	g	g/piece	M III KERN	DAkkS KERN
FXN 3K-4N	3	0,5	-	-	5	-	963-127
FXN 6K-3N	6	1	-	-	10	-	963-128
FXN 10K-3N	15	2	-	-	20	-	963-128
FXN 30K-3N	30	5	-	-	50	-	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

FXN 3K-3M	3	1	1	20	5	965-227	963-127
FXN 10K-3M	15	5	5	100	20	965-228	963-128
FXN 6K-3M	6	2	2	40	10	965-228	963-128
FXN 30K-2M	30	10	10	200	50	965-228	963-128

**CAL INT**  
**Internal adjusting**  
 Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)

**CAL EXT**  
**Adjusting program CAL**  
 For quick setting up of the balance's accuracy. External adjusting weight required

**ET**  
**EasyTouch**  
 Suitable for the connection, data transmission and control through PC or tablet

**MEMORY**  
**Memory**  
 Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.

**ALIBI**  
**Alibi memory**  
 Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.

**KUP**  
**KERN Universal Port (KUP)**  
 allows the connection of external KUP interface adapters, e.g. RS-232, RS-485, SB, Bluetooth, WIFI, Analogue, Ethernet etc. for the exchange of data and control commands, without installation effort

**RS 232**  
**RS-232 Data interface**  
 To connect the balance to a printer, PC or network

**RS 485**  
**RS-485 Data interface**  
 To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible

**USB**  
**USB Data interface**  
 To connect the balance to a printer, PC or other peripherals

**BT**  
**Bluetooth\* Data interface**  
 To transfer data from the balance to a printer, PC or other peripherals

**WIFI**  
**WIFI Data interface**  
 To transfer data from the balance to a printer, PC or other peripherals

**SWITCH**  
**Control outputs**  
 (optocoupler, digital I/O)  
 To connect relays, signal lamps, valves, etc.

**ANALOG**  
**Analogue interface**  
 to connect a suitable peripheral device for analogue processing of the measurements

**DUAL**  
**Interface for second balance**  
 For direct connection of a second balance

**LAN**  
**Network interface**  
 For connecting the scale to an Ethernet network

**KCP PROTOCOL**  
**KERN Communication Protocol (KCP)**  
 It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems

**GLP INTERN**  
**GLP/ISO log intern**  
 The balance displays weight, date and time, independent of a printer connection

**GLP PRINTER**  
**GLP/ISO log Printer**  
 With weight, date and time. Only with KERN printers.

**PCS**  
**Piece counting**  
 Reference quantities selectable. Display can be switched from piece to weight

**RECIPE A**  
**Recipe level A**  
 The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out

**RECIPE B**  
**Recipe level B**  
 Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display

**SUM A**  
**Totalising level A**  
 The weights of similar items can be added together and the total can be printed out

**PERCENT**  
**Percentage determination**  
 Determining the deviation in % from the target value (100 %)

**UNIT**  
**Weighing units**  
 Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details

**TOL**  
**Weighing with tolerance range (Checkweighing)**  
 Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model

**MOVE**  
**Hold function**  
 (Animal weighing program)  
 When the weighing conditions are unstable, a stable weight is calculated as an average value

**IP**  
**Protection against dust and water splashes IPxx**  
 The type of protection is shown in the pictogram

**UNDER**  
**Suspended weighing**  
 Load support with hook on the underside of the balance

**BATT**  
**Battery operation**  
 Ready for battery operation. The battery type is specified for each device

**ACCU**  
**Rechargeable battery pack**  
 Rechargeable set

**MULTI**  
**Universal plug-in power supply**  
 with universal input and optional input socket adapters for  
 A) EU, CH, GB  
 B) EU, CH, GB, US  
 C) EU, CH, GB, US, AUS

**230 V**  
**Plug-in power supply**  
 230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available

**230 V**  
**Integrated power supply unit**  
 Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request

**DMS**  
**Weighing principle Strain gauges**  
 Electrical resistor on an elastic deforming body

**T-FORK**  
**Weighing principle Tuning fork**  
 A resonating body is electromagnetically excited, causing it to oscillate

**FORCE**  
**Weighing principle Electromagnetic force compensation**  
 Coil inside a permanent magnet. For the most accurate weighings

**SC TECH**  
**Weighing principle Single cell technology**  
 Advanced version of the force compensation principle with the highest level of precision

**M +3 DAYS**  
**Conformity Assessment**  
 The time required for conformity assessment is specified in the pictogram

**DAkkS +3 DAYS**  
**DAkkS calibration possible (DKD)**  
 The time required for DAkkS calibration is shown in days in the pictogram

**ISO +4 DAYS**  
**Factory calibration (ISO)**  
 The time required for Factory calibration is shown in days in the pictogram

**1 DAY**  
**Package shipment**  
 The time required for internal shipping preparations is shown in days in the pictogram

**2 DAYS**  
**Pallet shipment**  
 The time required for internal shipping preparations is shown in days in the pictogram

\* The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.