

KERN OZM 544C832

KERN

First-class optics as well as strong illumination combined with a high level of flexibility and digital tools



| Category | |
|------------------|------------------------|
| Brand | Optics |
| Product category | Microscope |
| Product group | Digital microscope set |
| Product family | OZM-S |

| Approval | |
|----------|---|
| CE mark | ✓ |

| Construction | |
|-------------------------------|--------------------------------------|
| Dimension (W×D×H) | 330×285×510 mm |
| Optical system | Greenough |
| Tube type | Trinocular |
| Tube angle of inclination | 45° |
| Tube 360° rotation | ✓ |
| Diopter adjustment | both-sided |
| Diopter adjustment [Min] | -6 |
| Diopter adjustment [Max] | 6 |
| Contrasting methods | Bright field Darkfield (optional) |
| Light distribution | 100:0 |
| Interpupillary distance [Max] | 76 mm |
| Interpupillary distance [Min] | 52 mm |
| Camera type | USB3 Microscope camera - C-Mount |
| Camera sensor type | CMOS |
| Camera sensor size | 1/2,5" |
| Camera resolution | 5,1 MP |
| Camera colour depth | Colour |
| Camera framerate | 14,2 - 101,2 fps |
| Camera mounting types | C-mount thread |
| Camera - exposure method | Rolling Shutter |

| Ocular | |
|-----------------------|-------|
| Ocular field width | HSWF |
| Ocular magnifications | 10 x |
| Ocular visual field | 23 mm |
| Ocular diameter | 30 mm |

| Focussing | |
|---------------------|--------------|
| Torque regulation | ✓ |
| Working distance | 110 mm |
| Zoom [Min] | 0,7 x |
| Zoom [Max] | 4,5 x |
| Magnification ratio | 6,4:1 |
| Field of view [Min] | 5,1 mm |
| Field of view [Max] | 32,8 mm |
| Focusing mechanism | coarse drive |
| Sample height [Max] | 130 mm |

| Illumination | |
|------------------------------------------|-------------------------------------------------------------------------|
| Illumination type incident light | LED |
| Illumination intensity incident light | 3 W |
| Illumination intensity transmitted light | 3 W |
| Illumination type transmitted light | LED |
| Illuminance | Transmitted light Incident light + Transmitted light, separate |
| Illumination dimmable | |

| Functions | |
|------------------------------|-------------------------------------------------|
| Interfaces | USB 3.0 |
| Supported operating systems | Win XP Win Vista Win 7 Win 8 Win 10 |
| Camera - applicable software | external (OXM 901, OXM 902) |

| Power Supply | |
|---------------------------------------------------------------------------|-----------------------|
| Input voltage power supply / power [Max] | 100 - 240 V |
| Input voltage device / power [Max] | 100 - 240 V |
| Plug-in power supply type | Built-in power supply |
| Supplied power supply | Power supply unit |
| Plug-in power supply / adapter for countries - included with the delivery | EURO |

KERN OZM 544C832



First-class optics as well as strong illumination combined with a high level of flexibility and digital tools

| | |
|---------------------------------------------------------|-----|
| Plug-in power supply / adapter for countries - optional | AUS |
| | UK |
| | US |
| | CH |

Environmental conditions

| | |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 590×440×390 mm |
| Net weight | 5,5316 kg |
| Shipping method | Parcel service |
| Net weight approx. | 6 kg |
| Gross weight approx. | 8 kg |
| Shipping weight | 20,2 kg |

Pictograms